



# Introduction

A slip table is required for testing a specimen in its horizontal axis, or when a heavy specimen is to be tested. Slip tables are designed to achieve low friction in the driven axis, while supporting heavy loads and introducing minimum waveform distortion. All products from mechanical bearing to hydrostatic and hydraulic bearing slip table are all designed and built in-house, giving IMV full design control of this important part of a vibration test system.



# MB : Mechanical Bearing

Mechanical bearing employs the linear motion guide which incorporates a component with a linear rolling motion into practical use. It significantly contributes to high performance of table which are high-rigidity, high load and long stroke motion. Another strong feature of the mechanical bearing is easy to operate. Since it is light weighted and no need for a hydraulic unit.



Pitch Moment [N·m]

	MB	ST	TT-L	TT-H	TH
200 x 200	50	-	-	-	-
300 x 300	200	-	-	-	-
400 x 400	300	-	-	-	-
500 x 500	-	200	1,100	4,000	-
550 x 550	-	-	1,100	4,000	3,000
630 x 630	-	400	1,100	4,000	-
750 x 750	-	-	2,200	7,700	33,000
800 x 800	-	800	2,200	7,700	-
950 x 950	-	-	2,200	7,700	42,500
1000 x 1000	-	1,300	2,200	7,700	-
1150 x 1150	-	-	4,600	16,000	42,500
1200 x 1200	-	-	4,600	16,000	-
1450 x 1450	-	-	6,500	22,000	99,000
1500 x 1500	-	-	6,500	22,000	-
1800 x 1800	-	-	10,000	48,000	-
2000 x 2000	-	-	10,000	48,000	-

Maximum Load [kg]

	MB	ST	TT-L	TT-H	TH
200 x 200	30	-	-	-	-
300 x 300	30	-	-	-	-
400 x 400	50	-	-	-	-
500 x 500	-	200	200	800	-
550 x 550	-	-	200	800	1,500
630 x 630	-	300	300	1,200	-
750 x 750	-	-	400	1,600	9,000
800 x 800	-	400	400	1,600	-
950 x 950	-	-	500	2,000	9,000
1000 x 1000	-	500	500	2,000	-
1150 x 1150	-	-	-	2,000	9,000
1200 x 1200	-	-	500	2,000	-
1450 x 1450	-	-	-	2,000	9,000
1500 x 1500	-	-	500	2,000	-
1800 x 1800	-	-	800	3,000	-
2000 x 2000	-	-	800	3,000	-



See the movie on You Tube



See the movie on You Tube

